



# SL PASC 2


# SL PASC 4

Quick Guide  
Kurzanleitung  
Guide de démarrage rapide  
Guida rapida  
Instrucciones resumidas  
Instruções resumidas  
Beknopte gebruiksaanwijzing  
Krótka instrukcja obsługi  
Snabbguide


Kort vejledning  
Pikaohje  
Γρήγορος οδηγός  
Kisa Kılavuz  
Краткая инструкция  
快速指南  
快速使用指南  
クイックガイド  
퀵 가이드



4 x R-SMA



**SENNHEISER**



**Sennheiser Documentation App**



or online at  
[www.sennheiser.com/download](http://www.sennheiser.com/download)  
SpeechLine Digital Wireless\_



Sennheiser electronic GmbH & Co. KG

Am Labor 1, 30900 Wedemark, Germany  
[www.sennheiser.com](http://www.sennheiser.com)

Publ. 05/19, 583929/A01

## SL PASC 2


## Operating elements



## SL PASC 4



8 x R-SMA




## Specifications

	SL PASC 2	SL PASC 4
Frequency range	1,880 - 1,930 MHz	1,880 - 1,930 MHz
Insertion loss	- 4,5 dB typ.	- 8 dB typ.
Port to port isolation	22 dB min.	26 dB min.
Input / Output return loss	- 13 dB max	- 14 dB max
Connectors	AC coupled ports	AC coupled ports
Max. input power	1.5 W max	1.5 W max
Dimensions	150 x 50 x 21 mm	210 x 160 x 41 mm
Weight	135 g	663 g
Operating temperature	- 40 to 85°C	- 40 to 85°C
Relative humidity	max. 95 % (non-condensing)	max. 95 % (non-condensing)


**Connecting SL PASC 2**

2x SL Rack Receiver DW + AWM 2




**Connecting SL PASC 4**

A: 4x SL Rack Receiver DW + AWM 2



B: 8x SL Rack Receiver DW + AWM 4



**Sennheiser Documentation App**

ANDROID APP ON Google play

Available on the App Store

Instruction manual | Bedienungsanleitung | Notice d'emploi | Istruzioni per l'uso | Instrucciones de manejo | Manual de instruções | Gebruiksaanwijzing | Instrukcja obsługi | Bruksanvisning | Betjeningsvejledning | Käyttöohje | Ἐγχειρίδιο ὁδηγίας | Kullanim kılavuzu | Инст укция по эксплуатации | 使用说明书 | 取扱説明書 | 사용 설명서 |

or online at [www.sennheiser.com/download](http://www.sennheiser.com/download) [SpeechLine Digital Wireless\\_](#)