


XLR To TA6FLX Digital Adapter Cable



PIN ASSIGNMENTS



This cable is used to connect the input of the Lectrosonics DCHT Digital Camera Hop Transmitter to the AES3 digital output of a mixer or receiver. It is constructed with a TA6FLX jack, ultra-flexible cable and a 3-pin female XLR connector. The connectors have soldered connections to the cable, allowing them to be serviced or replaced if the need arises.

- Connectors:
- 6-pin TA6F female
 - XLR-3 female

Cable: Shielded, 0.176 in. OD

Length: 18 inches

